
your BEST camera module partner

### **KLT-D3MA-IMX258 V2.6**

### 13MP Sony IMX258 4-Layer MIPI Interface Auto Focus Camera Module



Front View

**Back View** 

### **Specifications**

Camera Module No.	KLT-D3MA-IMX258 V2.6		
Resolution	13MP		
Image Sensor	IMX258		
Sensor Type	1/3.06"		
Pixel Size	1.12 um x 1.12 um		
EFL	3.85 mm		
F.NO	2.20		
Pixel	4224 x 3136		
View Angle	74.4°(DFOV) 62.7°(HFOV) 48.7°(VFOV)		
Lens Dimensions	8.50 x 8.50 x 5.37 mm		
Module Size	20.85 x 8.50 mm		
Module Type	Auto Focus		
Interface	4-Layer MIPI		
Auto Focus VCM Driver IC	DW9763		
Lens Type	650nm IR Cut		
Operating Temperature	-20°C to +70°C		
Mating Connector	BBR43-30KB533		

www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



### **KLT-D3MA-IMX258 V2.6**


13MP Sony IMX258 4-Layer MIPI Interface Auto Focus Camera Module



Top View



Side View



**Bottom View** 




Mating Connector

www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778




### your BEST camera module partner




www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778






www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778





www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



## SONY

## [Product Brief]

### Ver.1.0

# IMX258

Diagonal 5.867 mm (Type 1/3.06) 13Mega-Pixel CMOS Image Sensor with Square Pixel for Color Cameras

#### Description

IMX258 is a diagonal 5.867mm (Type 1/3.06) 13 Mega-pixel CMOS active pixel type stacked image sensor with a square pixel array. It adopts Exmor RS<sup>™</sup> technology to achieve high speed image capturing by column parallel A/D converter circuits and high sensitivity and low noise image (comparing with conventional CMOS image sensor) through the backside illuminated imaging pixel structure. R, G, and B pigment primary color mosaic filter is employed. By introducing spatially multiplexed exposure technology, high dynamic range still pictures and movies are achievable. It

equips an electronic shutter with variable integration time. It operates with three power supply voltages: analog 2.7 V, digital 1.2 V and 1.8 V for input/output interface and achieves low power consumption.

In addition, this product is designed for use in cellular phone and tablet pc. When using this for another application, Sony does not guarantee the quality and reliability of product. Therefore, don't use this for applications other than cellular phone and tablet pc. Consult your Sony sales representative if you have any questions.

### **Functions and Features**


- Back-illuminated and stacked CMOS image sensor Exmor RSTM
- Phase Detection pixel data output for Phase Detection Auto Focus
- High Dynamic Range (HDR) mode with raw data output.
- High signal to noise ratio (SNR).
- ◆ Full resolution @30fps (Normal / HDR). 4K2K @30fps (Normal / HDR) 1080p @60fps (Normal )
- Output video format of RAW10/8.
- Pixel binning readout and V sub-sampling function.
- Independent flipping and mirroring.
- CSI-2 serial data output (MIPI 2lane/4lane, Max. 1.3Gbps/lane, D-PHY spec. ver. 1.1 compliant)
- ◆ 2-wire serial communication.
- Two PLLs for independent clock generation for pixel control and data output interface.
- Dynamic Defect Pixel Correction.
- Fast mode transition. (on the fly)
- Dual sensor synchronization operation.
- 4K bit of OTP ROM for users.
- Built-in temperature sensor.

#### **Device Structure**

- CMOS image sensor
- Image size :
- Total number of pixels :
- Number of effective pixels :
- Number of active pixels :
- Chip size :
- Unit cell size :
- Substrate material :

Diagonal 5.867 mm (Type 1/3.06) 4224 (H) × 3192 (V) approx. 13.48 M pixels 4224 (H) × 3144 (V) approx. 13.28 M pixels 4208 (H) × 3120 (V) approx. 13.13 M pixels 5.990 mm (H) × 3.908 mm (V) 1.12  $\mu$ m (H) × 1.12  $\mu$ m (V) Silicon

System block diagram





\* Exmor RS is a trademark of Sony Corporation. The Exmor RS is a Sony's CMOS image sensor with high-resolution, high-performance and compact size by replacing a supporting substrate in Exmor R<sup>™</sup> which changed fundamental structure of Exmor <sup>™</sup> pixel adopted column parallel A/D converter to back-illuminated type, with layered chips formed signal processing circuits.

### 1. General Description

The DW9763 is a single 10-bit DAC with 100mA output current sinking capability and embedded 8KByte eFlash memory. Designed for linear control of voice coil motors, the DW9763 is capable of operating voltage up to 3.3V.

The SAC (Smart Actuator Control) mode is applied to minimize the mechanical vibration. The SAC mode highly improves the actuator's settling time and tolerance coverage compared with conventional LSC (Linear Slope Control) mode. The DAC and eFlash are controlled via an I2C compatible serial interface.

The DW9763 incorporates with a POR (Power On Reset) circuit, power down mode. POR circuit gets to operate when VDD (supply power) turns on. The output current keeps 0mA until valid register value takes place. During the power down mode, it consumes current max.1uA.


The DW9763 is designed for auto focus and optical zoom for mobile camera, digital still camera, camcorders and other nano actuator applications.

### Features

10 bit resolution current sinking of 100mA for VCM SAC (Smart Actuator Control) mode Supply voltage range (VDD) : 2.3V to 3.3V Fast mode I2C interface compatible (1.8V interface available) Power down mode Power on reset (POR) Embedded 8KByte eFlash memory Package : 8 pin WLCSP Package Size : 0.77mm X 1.75mm X 0.3mm


### Applications

Mobile camera Digital still camera Camcorder Web camera Nano actuator



	n a geme n	substances	relatec	environment-related
	04-01 REV.	ING DWG NO.	DRAWI	TOMER
	BAR SIZE A3	10 '	04/24/10	DICK.LEE
I	.4*HI.0mm BOARD TO BOARD CONN.RECEPTACLE WITHOUT HOLD DOWN	F 10 ` P0.	04/24/10'	HARDWARE
Π		TITLE	04/15/10 DATE	CHECKED
				DESIGN
		10	04/15/10	
	MATERIAL / FINISH	PART #		0
	HIGH TEMP RESIN/UL 94 V-0	- BBR 4 3 - I X X X 3 3	  -B	
	COPPER ALLOY/PLATING GOLD	T - BBR 4 3 - 100 X 30	ХХ Т-ВI	
Ш				
				LACES
C				
כ		(		
		2)	/	/
C	(			
			6 R	

			XI, AXI 05/13/13'	ASE PER NPRI0009 11/05/10'	SCRIPTION DATE	7
			RAIN	RAIN	DRAWN	
			eng Jeff	DICK.SON HARDWARE	CHECKED	ω
			Jeff Date 2013.11.14	HARDWARE	CHECKED APPROVED	
	כ	>				



CUSTOMER DRAWING DWG NO. DRAWN RAIN DESIGN RAIN HARDWARE HECKED wironment-related substances management technical standard ICK.LEE PROVED  $\Box$ DATE 04/24/10′ DATE 04/15/10′ DATE 04/15/10 ' 04/24/10' TABLE A: POSITIONS DATE 422 5 80 70 60 54 50 48 44 40 34 32 30 26 24 20  $\overline{0}$  $\infty$ SERIES . 4 10.61  $\overline{\infty}$ 12.21 8.61 A MIG 4 2 9.41 ف 7.41 7.01 6 -б.  $\overline{\omega}$ 9 5 P0.4\*H1.0mm BOARD TO BOARD CONN.RECEPTACLE WITHOUT HOLD DOWN . 0\_\_\_ ~\_\_\_\_ 2 6 . 6\_\_\_  $\infty$ . ი . \_\_\_\_\_ . 6 | .4 C - BBR 4 3 - 0 4 - 0 I ADVANCED \_ 7.60 6.40 6.00 DIM B 5 9 5.60 4 ς.  $\sim$ 13.60 0 ق 4 4 ω  $\sim$ BBR  $\infty$ 60 20 40 . 00 60 . 80 80 20 40 60 . 4 . 60 60 .40 ||.7| |7.7| 15.71 12.51 |3.7| ||.3| 10.51 9.71 8.5I 8. . 7.71 6.91 6.5I 6. || 5.71 4.91 4.51 3.71 DIM C <u>с</u> . Ω I ZE A3 Ш D C  $\triangleright$ П

ω



### your BEST camera module partner


#### **Cameras Applications**







Video Conference



Live Streaming

Eye Tracker Biometric Detection

Machine Vision

Agricultural Monitor



Night Vision Security

Drone and Sports Eagle Eyes




Interactive Pet Camera

www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



### **Cameras Applications**

### your BEST camera module partner



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



#### **Camera Module Pinout Definition Reference Chart**

	ptina Himax GalaxyCore PixArt SmartSens Sensor		
Pin Signal	Description		
DGND GND	ground for digital circuit		
AGND	ground for analog circuit		
PCLK DCK	DVP PCLK output		
XCLR PWDN XSHUTDOWN STANDBY	power down active high with internal pull-down resistor		
MCLK XVCLK XCLK INCK	system input clock		
RESET RST	reset active low with internal pull-up resistor		
NC NULL	no connect		
SDA SIO_D SIOD	SCCB data		
SCL SIO_C SIOC	SCCB input clock		
VSYNC XVS FSYNC	DVP VSYNC output		
HREF XHS	DVP HREF output		
DOVDD	power for I/O circuit		
AFVDD	power for VCM circuit		
AVDD	power for analog circuit		
DVDD	power for digital circuit		
STROBE FSTROBE	strobe output		
FSIN	synchronize the VSYNC signal from the other sensor		
SID	SCCB last bit ID input		
ILPWM	mechanical shutter output indicator		
FREX	frame exposure / mechanical shutter		
GPIO	general purpose inputs		
SLASEL	I2C slave address select		
AFEN	CEN chip enable active high on VCM driver IC		
MIPI Interface			
MDN0 DN0 MD0N DATA N DMO1N	MIPI 1st data lane negative output		
MDP0 DP0 MD0P DATA P DMO1P	MIPI 1st data lane positive output		
MDN1 DN1 MD1N DATA2 N DMO2N	MIPI 2nd data lane negative output		
MDP1 DP1 MD1P DATA2 P DMO2P	MIPI 2nd data lane positive output		
MDN2 DN2 MD2N DATA3 N DMO3N	MIPI 3rd data lane negative output		
MDP2 DP2 MD2P DATA3 P DMO3P	MIPI 3rd data lane positive output		
MDN3 DN3 MD3N DATA4 N DMO4N	MIPI 4th data lane negative output		
MDP3 DP3 MD3P DATA4 P DMO4P	MIPI 4th data lane positive output		
MCN CLKN CLK_N DCKN	MIPI clock negative output		
MCP CLKP MCP CLK P DCKN	MIPI clock positive output		
DVP Parallel Interface	· ····································		
D0 D00 Y0	DVP data output port 0		
D1 D01 Y1	DVP data output port 1		
D2 D02 Y2	DVP data output port 2		
D3 D03 Y3	DVP data output port 2 DVP data output port 3		
D4 D04 Y4	DVP data output port 4		
D5 D05 Y5	DVP data output port 5		
D6 D06 Y6	DVP data output port 6		
D7 D07 Y7	DVP data output port 7		
D8 D08 Y8	DVP data output port 8		
D9 D09 Y9	DVP data output port 8 DVP data output port 9		
D9 D09 19 D10 D010 Y10	DVP data output port 9 DVP data output port 10		
D11 D011 Y11	DVP data output port 10		
ווו ווסם ווס	עטורי עמומ טעוףער אטור דו		

www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



### **Camera Reliability Test**

Reliability Inspection Item			Ta atia a Matha d	Accontance Criteria	
Category		Item	Testing Method	Acceptance Criteria	
	Storage	High 60°C 96 Hours	Temperature Chamber	No Abnormal Situation	
	Temperature	Low -20°C 96 Hours	Temperature Chamber	No Abnormal Situation	
	Operation	High 60°C 24 Hours	Temperature Chamber	No Abnormal Situation	
Environmental	Temperature	Low -20°C 24 Hours	Temperature Chamber	No Abnormal Situation	
Environmental	Humidity	60°C 80% 24 Hours	Temperature Chamber	No Abnormal Situation	
	Thermal Shock	High 60°C 0.5 Hours Low -20°C 0.5 Hours Cycling in 24 Hours	Temperature Chamber	No Abnormal Situation	
	Drop Test	Without Package 60cm	10 Times on Wood Floor	Electrically Functional	
	(Free Falling)	With Package 60cm	10 Times on Wood Floor	Electrically Functional	
	Vibration Test	50Hz X-Axis 2mm 30min	Vibration Table	Electrically Functional	
Dhysiaal		50Hz Y-Axis 2mm 30min	Vibration Table	Electrically Functional	
Physical		50Hz Z-Axis 2mm 30min	Vibration Table	Electrically Functional	
	Cable Tensile Strength Test Cable Tensile Cycling in 24 Hours		Tensile Testing Machine	Electrically Functional	
		Contact Discharge 2 KV	ESD Testing Machine	Electrically Functional	
Electrical	ESD Test	Air Discharge 4 KV	ESD Testing Machine	Electrically Functional	
	Aging Test	On/Off 30 Seconds Cycling in 24 Hours	Power Switch	Electrically Functional	
	USB Connector	On/Off 250 Times	Plug and Unplug	Electrically Functional	



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778

### **Camera Inspection Standard**

г

### your BEST camera module partner

Inspection Item		n Item	Inspection Method	Standard of Inspection	
Category		ltem	inspection method		
		Color	The Naked Eye	Major Difference is Not Allowed.	
	FPC/ PCB	Be Torn/Chopped The Naked Eye Copper Crack Exposure is Not A		Copper Crack Exposure is Not Allowed.	
		Marking	The Naked Eye	Clear, Recognizable (Within 30cm Distance)	
Appearance	Holder	Scratches	The Naked Eye	The Inside Crack Exposure is Not Allowed	
		Gap	The Naked Eye	Meet the Height Standard	
		Screw	The Naked Eye	Make Sure Screws Are Presented (If Any)	
		Damage	The Naked Eye	The Inside Crack Exposure is Not Allowed	
		Scratch	The Naked Eye	No Effect On Resolution Standard	
	Long	Contamination	The Naked Eye	No Effect On Resolution Standard	
	Lens	Oil Film	The Naked Eye	No Effect On Resolution Standard	
		Cover Tape	The Naked Eye	No Issue On Appearance.	
		No Communication	Test Board	Not Allowed	
		Bright Pixel	Black Board	Not Allowed In the Image Center	
		Dark Pixel	White board	Not Allowed In the Image Center	
		Blurry	The Naked Eye	Not Allowed	
		No Image	The Naked Eye	Not Allowed	
	Image	Vertical Line	The Naked Eye	Not Allowed	
		Horizontal Line	The Naked Eye	Not Allowed	
Function		Light Leakage	The Naked Eye	Not Allowed	
		Blinking Image	The Naked Eye	Not Allowed	
		Bruise	Inspection Jig	Not Allowed	
		Resolution	Chart	Follows Outgoing Inspection Chart Standard	
		Color	The Naked Eye	No Issue	
		Noise	The Naked Eye	Not Allowed	
		Corner Dark	The Naked Eye	Less Than 100px By 100px	
		Color Resolution	The Naked Eye	No Issue	
		Height	The Naked Eye	Follows Approval Data Sheet	
		Width	The Naked Eye	Follows Approval Data Sheet	
Dimer	ISION	Length	The Naked Eye	Follows Approval Data Sheet	
		Overall	The Naked Eye	Follows Approval Data Sheet	


www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **KLT Package Solutions**

### **KLT** Camera Module




Tray with Grid and Space





Place Cameras on the Tray





www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **Camera Modules Package Solution**

Full Tray of Cameras




Put Tray into Anti-Static Bag

Cover Tray with Lid



Vacuum the Anti-Static Bag





www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **Camera Modules Package Solution**

Sealed Vacuum Bag with Labels 1. Model and Description 2. Quantity 3. Shipping Date 4. Caution



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### Large Order Package Solution

Place Foam Sheets Between Trays

Foam Sheets are Slightly Larger than Trays



Place Foam Sheets and Trays into Box

Foam Sheets are Tightly Fitting Box



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **Small Order Package Solution**

Place Foam Sheets and Trays into Small Box

Foam Sheets are Nicely Fitting the Small Box



Package in Small Box for Shipment

Place Small Boxes into Larger Box



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **Carbon Box Package Solution**

Seal the Carbon Box

Final Package Labelled Box



**Carbon Box Ready for Shipment** 

1. Delivery Address and Phone No. 2. Box No. and Ship Date 3. Fragile Caution



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### Sample Order Package Solution

Place Sample into Small Anti-Static Bag

Place Connectors into Small Ant-Static Bag





### Sample Labels on the Small Bag 1. Camera Module or Connector Model 2. Shipping Date and Quantity 3. Caution



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778



your BEST camera module partner

### **Connectors Large Order Package Solution**

Connectors in a Wheel



The Wheel is Perfectly Fitting the Box

Label Connectors in the Wheel



**Connectors Box Ready for Shipment** 



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778

#### Company Kai Lap Technologies (KLT)

Kai Lap Technologies Group Limited. (KLT) was established in 2009, a next-generation technology driven manufacturer specialized in research, design, and produce of audio and video products. KLT is occupying 20,000 square feet automated plants with 100 employees of annual throughput 30,000,000 units cameras.

KLT provides OEM, ODM design, contract manufacturing, and builds the camera products. You may provide the requirements to us, even with a hand draft, our sales and engineering work together to meet your needs. We consider ourselves your last-term partner in developing practical and innovative solutions.

Our team covers everything from initial concept development to mass produced product. KLT specializes in customized camera design, raw material, electronic engineering, firmware/software development, product testing, and packing design. Our experienced strategic supply systems offer a robust and dependable manufacturing capacity for orders of various sizes.



#### **Limited Warranty**

KLT provides the following limited warranty if you purchased the Product(s) directly from KLT company or from KLT's website, <u>www.KaiLapTech.com</u>. Product(s) purchased from other sellers or sources are not covered by this Limited Warranty. KLT guarantees that the Product(s) will be free from defects in materials and workmanship under normal use for a period of one (1) year from the date you receive the product ("Warranty Period").

For all Product(s) that contain or develop material defects in materials or workmanship during the Warranty Period, KLT will, at its sole option, either: (i) repair the Product(s); (ii) replace the Product(s) with a new or refurbished Product(s) (replacement Product(s) being of identical model or functional equivalent); or (iii) provide you a refund of the price you paid for the Product(s).

This Limited Warranty of KLT is solely limited to repair and/or replacement on the terms set forth above. KLT is not reliable or responsible for any subsequential events.



# KIT

## CMOS CAMERA MODULES

your BEST camera module partner

#### **KLT Strength**

**Powerful Factory** 



#### **Professional Service**



### **Promised Delivery**



www.KaiLapTech.com sales@KaiLapTech.com Tel: (852) 6908 1256 Fax: (852) 3017 6778